

Cross beam pair LNS-DUO 100×50, Cross-beam length: 2700mm



Order data

| | |
|--------------|---------------|
| Order number | 991338 2700 |
| GTIN | 4058255037407 |
| Item class | 96P |

Description

Version:

Box section, cold-rolled profiles with welded-on engagement posts. Each engagement post has up to 5 sturdy hooks, for optimum weight distribution across the pallet racking stiles. Load capacity up to 3060 kg per cross beam pair.

Supplied with:

2 cross beams for insertion into the frame stiles, each with 2 locking pins.

Colour:

RAL 2004 pure orange, **powder-coated**.

Note:

If new cross beams with depth 50 mm are to be combined with the old cross beams with depth 40 mm, they must be fitted in pairs.

Technical description

| | |
|---------------------------------------|-------------------------|
| Application range | Rack |
| Cross-beam type: | LNS-DUO 100×50 |
| Cross-beam length | 2700 mm |
| Load capacity per pair of cross beams | 1545 kg |
| Cross beam height | 100 mm |
| Type of product | Cross beam / cross rail |