

Cross beam pair EGN-DUO 120×50, Cross-beam length: 2700mm**Order data**

Order number	991346 2700
GTIN	4058255037421
Item class	96P

Description**Version:**

Box section, cold-rolled profiles with welded-on engagement posts. Each engagement post has up to 5 sturdy hooks, for optimum weight distribution across the pallet racking stiles. Load capacity up to 3060 kg per cross beam pair.

Supplied with:

2 cross beams for insertion into the frame stiles, each with 2 locking pins.

Colour:

RAL 2004 pure orange, **powder-coated**.

Note:

If new cross beams with depth 50 mm are to be combined with the old cross beams with depth 40 mm, they must be fitted in pairs.

Technical description

Application range	Rack
Load capacity per pair of cross beams	3060 kg
Cross-beam length	2700 mm
Cross-beam type:	LNS-DUO 120×50
Cross beam height	120 mm
Type of product	Cross beam / cross rail