

Cross beam pair LNS-DUO 110×50, Cross-beam length: 2700mm



Order data

Order number	991342 2700
GTIN	4058255037414
Item class	96P

Description

Version:

Box section, cold-rolled profiles with welded-on engagement posts. Each engagement post has up to 5 sturdy hooks, for optimum weight distribution across the pallet racking stiles. Load capacity up to 3060 kg per cross beam pair.

Supplied with:

2 cross beams for insertion into the frame stiles, each with 2 locking pins.

Colour:

RAL 2004 pure orange, **powder-coated**.

Note:

If new cross beams with depth 50 mm are to be combined with the old cross beams with depth 40 mm, they must be fitted in pairs.

Technical description

Cross-beam length	2700 mm
Cross-beam type:	LNS-DUO 110×50
Application range	Rack
Load capacity per pair of cross beams	2460 kg
Cross beam height	110 mm
Type of product	Cross beam / cross rail