



## COLOUR MATCH LED true colour work lamps, Type: SUN4



### Order data

Order number	081513 SUN4
GTIN	5708997356579
Item class	08C

### Description

#### Version:

**COLOUR MATCH.** Special LED with high CRI value for **perfect colour reproduction** and extremely long LED working life. Perfect for all painting, polishing, cleaning and preparation work. Designed for use in paint shops. **Exchangeable glass lens** and resistant to all types of solvent, even when cleaned every day. **SUNMATCH 4.** Handy cordless LED work lamp with 180° flexible lamp head for preparation and colour matching. With stepless CCT SCAN function. With stepless CCT SCAN function. When activated, the lamp automatically scans the surface of the object with the entire colour spectrum range. Locking is possible at any time. Ideal for detecting paint defects.

#### Function:

IP65: Protected against jets of water from all directions and protected against penetration by dust (dust-tight), also completely protected against touching.

#### Supplied with:

Supplied with charger and charging station.

### Technical description

CRI value	95
Light colour	true colour

Weight	270 g
IP Index of Protection	IP 65
ATEX zone	no
Battery voltage	3.7 V
Overall length	203 mm
Type of rechargeable battery	Lithium-ion
Number of rechargeable batteries contained	1
Illumination time	2 - 10 h
Power supply	Rechargeable battery powered
Battery capacity	2.6 Ah
Manufacturer's designation	SUNMATCH 4
Illumination	50 - 500 lm
Overall width	89 mm
Type of product	Work lamp