

**Angle grinder GWS, Type: 30-230PB****Order data**

Order number	077153 30-230PB
GTIN	4059952609102
Item class	03C

Description**Version:****Powerful 230 mm angle grinder:**

- **Powerful motor with constant-speed electronics, smooth start-up and inrush current limitation.**
- **High protection of the user by vibration control on the main and auxiliary handles, kick-back stop and restart inhibit.**
- **Adjustable grasp handle for optimum grinding and cutting.**
- **SDS quick-clamping nut and spindle lock.**

Advantage:**Less downtime due to maintenance work**

- **thanks to its compact design and brushless 2800 watt motor.**

High application protection and comfort

- **Brake.**
- **KickBack Control.**
- **Restart Protection.**
- **Smooth start-up.**
- **Tool-less adjustment of safety guard.**
- **Anti-vibration side handle.**

LED display:

LED display helps user optimise way of working.

Power cable:

4 meter cable length for increased comfort on-site.

Vibration Cancelling Technology:

The vibration-cancelling system achieves the lowest vibration values in this product segment and enables non-fatiguing work.

PROtection switch:

Immediate tool deactivation when the switch is released.

Supplied with:

Supplied with protective hood, additional handle.

With SDS quick-clamping nut.

Technical description

Power consumption	2800 W
Cable length	4 m
maximum vibration to EN	5 m/s ²
Kick-back stop	yes
Manufacturer's designation	GWS 30-230 PB
Width	334 mm
Nominal voltage	230 V
Length	524 mm
Special features	Braking system
Special features	PROtection switch
Power supply	Mains-powered
Restart block	yes
Dead man's circuit	yes
maximum cutting depth	59 mm
Soft start	yes
Weight	5.9 kg
Connection thread	M14
Height	139 mm
maximum disc Ø	230 mm
maximum speed	6500 min ⁻¹
Type of product	Angle grinder

