

Garant GRIDLINE

**Workstation eLevel with pale Eterlux worktop, Length: 1500/2mm****Order data**

Order number	920014 1500/2
GTIN	4067263001393
Item class	91P

**Description****Version:**

**Workstation eLevel** height steplessly adjustable electrically. Height adjustment by an electronic control panel. Control panel with display and memory functions. Push-button adjustment for a suitable **height of the entire workstation**.

**Colour:**

**Support leg** RAL 7016 anthracite, **not configurable**.

**Lift column** anodised aluminium, **not configurable**.

**Side and rear wall** RAL 7035 light grey **powder-coated, configurable**.

**Note:**

- **If using casings attached to the underside of the worktop, note that such casings may not exceed a maximum height of 500 mm.**
- **Caution: when installing benches in a row, please use side plates no. 920350 (crush hazard).**

Sizes with .../2 are fitted with an alternative lift unit. Technical data is similar to the previous lift units, slight deviations. Control panel is visually different for these sizes, but functionally the same.

- **Entry of these article numbers only after prior consultation with Technical Purchasing P93, Tel. +49 89 8391 9165, current availability must be checked.**
- **Observe the maximum load capacity, under no circumstances must it be exceeded! Particularly important in the planning of support column structures.**

**Technical description**

Worktop covering	Eterlux (melamine / phenolic resin)
Coating thickness	2.7 mm
Weight	80 kg
Worktop thickness	40 mm
Principle of height adjustment	complete structure
Model	eLevel
Worktop depth	800 mm
Material of worktop	Eterlux
Series	Workstation
Worktop length	1500 mm
Height adjustment range (worktop surface) from – to	670 - 990 mm
Colour of worktop surface	pale grey
Width	1500 mm
Stepless height adjustment	yes
Plug type, input	F
Surface worktop	Coating very scratch-resistant and heat-resistant
Control panel with display and memory functions	yes
Nominal voltage	250 V
Depth	800 mm
Height adjustment workstation	670-990 mm
Design version	Steel hollow section construction
Workbench/desk load capacity - maximum distributed load (on wood)	250 kg
Type of height adjustment	electrical
Insert thickness	40 mm
Height adjustment	25 mm
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of product	Work table

