

Garant GRIDLINE

eLevel workstation with dark grey Eluplan worktop, Length: 2000/2mm**Order data**

Order number	920012 2000/2
GTIN	4067263001379
Item class	91P

Description**Version:**

Workstation eLevel height steplessly adjustable electrically. Height adjustment by an electronic control panel. Control panel with display and memory functions. Push-button adjustment for a suitable **height of the entire workstation**.

Colour:

Support leg RAL 7016 anthracite, **not configurable**.

Lift column anodised aluminium, **not configurable**.

Side and rear wall RAL 7035 light grey **powder-coated, configurable**.

Note:

- **If using casings attached to the underside of the worktop, note that such casings may not exceed a maximum height of 500 mm.**
- **Caution: when installing benches in a row, please use side plates no. 920350 (crush hazard).**

Sizes with .../2 are fitted with an alternative lift unit. Technical data is similar to the previous lift units, slight deviations. Control panel is visually different for these sizes, but functionally the same.

- **Entry of these article numbers only after prior consultation with Technical Purchasing P93, Tel. +49 89 8391 9165, current availability must be checked.**
- **Observe the maximum load capacity, under no circumstances must it be exceeded! Particularly important in the planning of support column structures.**

Technical description

Nominal voltage	250 V
Worktop thickness	40 mm
Principle of height adjustment	complete structure
Depth	800 mm
Control panel with display and memory functions	yes
Model	eLevel
Surface worktop	Coating anti-static, highly abrasion-resistant, medium hardness, not colour-fast
Material of worktop	Eluplan
Height adjustment range (worktop surface) from – to	670 - 990 mm
Width	2000 mm
Worktop depth	800 mm
Plug type, input	F
Stepless height adjustment	yes
Worktop length	2000 mm
Coating thickness	2 mm
Worktop covering	Eluplan (plastic), (linoleum covering)
Series	Workstation
Colour of worktop surface	dark grey
Weight	93 kg
Height adjustment workstation	670-990 mm
Design version	Steel hollow section construction
Workbench/desk load capacity - maximum distributed load (on wood)	250 kg
Type of height adjustment	electrical
Insert thickness	40 mm
Height adjustment	25 mm
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of product	Work table

