

Garant GRIDLINE

eLevel+ workstation with dark grey Eluplan worktop, Length: 1000/2mm**Order data**

Order number	920022 1000/2
GTIN	4067263001447
Item class	91P

Description**Version:**

Workstation eLevel+ height steplessly adjustable electrically. Height adjustment via an electronic control panel. Control panel with display and memory function. Push-button adjustment for a suitable worktop height.

Colour:

Support leg RAL 7016 anthracite, **not configurable**.

Lift column anodised aluminium, **not configurable**.

Side and rear wall RAL 7035 light grey **powder-coated, configurable**.

Note:

- **If using casings attached to the underside of the worktop, note that such casings may not exceed a maximum height of 500 mm.**
- **Caution: when installing benches in a row, please use side plates no. 920350 (crush hazard).**

Sizes with .../2 are fitted with an alternative lift unit. Technical data is similar to the previous lift units, slight deviations. Control panel is visually different for these sizes, but functionally the same.

- **Entry of these article numbers only after prior consultation with Technical Purchasing P93, Tel. +49 89 8391 9165, current availability must be checked.**
- **Observe the maximum load capacity, under no circumstances must it be exceeded! Particularly important in the planning of support column structures.**

Technical description

Height with rear panel	1000 mm
Worktop length	1000 mm
Plug type, input	F
Control panel with display and memory functions	yes
Model	eLevel+
Worktop depth	700 mm
Surface worktop	Coating anti-static, highly abrasion-resistant, medium hardness, not colour-fast
Weight	78 kg
Width	1000 mm
Worktop thickness	40 mm
Worktop covering	Eluplan (plastic), (linoleum covering)
Coating thickness	2 mm
Stepless height adjustment	yes
Height adjustment range (worktop surface) from – to	670 - 990 mm
Nominal voltage	250 V
Depth	800 mm
Series	Workstation
Material of worktop	Eluplan
Principle of height adjustment	only with worktop
Colour of worktop surface	dark grey
Height adjustment workstation	670-990 mm
Design version	Steel hollow section construction
Workbench/desk load capacity - maximum distributed load (on wood)	250 kg
Type of height adjustment	electrical
Insert thickness	40 mm
Height adjustment	25 mm

Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of product	Work table