

Garant GRIDLINE

## Workstation eLevel+ with pale Eterlux worktop, Length: 1000/2mm



### Order data

Order number	920024 1000/2
GTIN	4067263001478
Item class	91P

### Description

#### Version:

**Workstation eLevel+** height steplessly adjustable electrically. Height adjustment via an electronic control panel. Control panel with display and memory function. Push-button adjustment for a suitable worktop height.

#### Colour:

**Support leg** RAL 7016 anthracite, **not configurable**.

**Lift columns** anodised aluminium, **not configurable**.

**Side panel and rear panel** RAL 7035 light grey **powder-coated, configurable**.

#### Note:

- **If using casings attached to the underside of the worktop, note that such casings may not exceed a maximum height of 500 mm.**
- **Caution: when installing benches in a row, please use side plates no. 920350 (crush hazard).**

Sizes with .../2 are fitted with an alternative lift unit. Technical data is similar to the previous lift units, slight deviations. Control panel is visually different for these sizes, but functionally the same.

- **Entry of these article numbers only after prior consultation with Technical Purchasing P93, Tel. +49 89 8391 9165, current availability must be checked.**
- **Observe the maximum load capacity, under no circumstances must it be exceeded! Particularly important in the planning of support column structures.**

### Technical description

Series	Workstation
Nominal voltage	250 V
Worktop depth	700 mm
Weight	78 kg
Colour of worktop surface	pale grey
Height adjustment range (worktop surface) from – to	670 - 990 mm
Model	eLevel+
Stepless height adjustment	yes
Width	1000 mm
Coating thickness	2.7 mm
Worktop length	1000 mm
Worktop thickness	40 mm
Worktop covering	Eterlux (melamine / phenolic resin)
Plug type, input	F
Principle of height adjustment	only with worktop
Control panel with display and memory functions	yes
Material of worktop	Eterlux
Surface worktop	Coating very scratch-resistant and heat-resistant
Depth	800 mm
Height with rear panel	1000 mm
Height adjustment workstation	670-990 mm
Design version	Steel hollow section construction
Workbench/desk load capacity - maximum distributed load (on wood)	250 kg
Type of height adjustment	electrical
Insert thickness	40 mm
Height adjustment	25 mm
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003

Type of product

Work table