


**TMSERROR, Type: GBH1821**

**Order data**

Order number	075515 GBH1821
GTIN	4059952528113
Item class	03B

**Description**
**Version:**

**18-V cordless hammer drill** with **SDS-plus tool mounting** and brushless motor.

- **Overload clutch to protect both user and machine.**
- **Reversible.**
- **Extremely sturdy: Electronic Motor Protection switches off the motor if it is overloaded. Fully operational even after a drop test from 2 m on to concrete.**

**Supplied with:**

Cordless hammer drill GBH 18V-21 Professional, 2 pcs. 18V / 4.0 Ah rechargeable battery, GAL 18V-40 charger, L-BOXX.

**Note:**

Suitable carbide hammer drills can be found from No. 787000. Suitable spare batteries and chargers can be found under No. 073851 – 073866.

**Technical description**

Number of rechargeable batteries contained	2
Type of rechargeable battery	Lithium-ion
Weight without battery	2.4 kg
suitable battery - supplier / battery type / voltage	Bosch 18 V
maximum twist drill size Ø in wood	30 mm
Impact energy	2 J

Packaging	Modular case (L-Boxx)
maximum twist drill size Ø in concrete	21 mm
Speed range	0 - 1800 min <sup>-1</sup>
Battery capacity	4 Ah
Power supply	Rechargeable battery-powered
maximum twist drill size Ø in steel	13 mm
Manufacturer's designation	GBH 18V-21
Battery voltage	18 V
Tool arbor shape	SDS-Plus
maximum hammer rate	5100 min <sup>-1</sup>
Weight including rechargeable battery	5.5 kg
Type of product	Hammer drill

---

## Accessories

Li-ion battery Battery type, battery voltage B18 V	073853 B18
--	------------