



Safety shut-off External thread, Connection external thread: 1/4in



Order data

Order number	080285 1/4
GTIN	7391390044785
Item class	08A

Description

Version:

Steel couplings have many advantages in pneumatic systems compared to standard brass couplings:

- **Easy to use with only one hand with low coupling force.**
- **High flow rates as a consequence of very low pressure drop.**
- **Long working life due to surface treatment and hardened components with tight manufacturing tolerances.**
- **Cost-effectiveness – the amortisation time is 2 years at the most.**

The **eSafe safety coupling** satisfies the ISO standard 4414 and EN 983. It is first depressurised and then decoupled in a second step (no whiplash). New improved single-handed operation. Rate of flow: 2250 ltr/min, maximum operating pressure 16 bar.

Application:

For improving the performance, economics, and safety of industrial compressed air installations.

Note:

The CEJN series 320 satisfies Euro standard 7.6 (nominal Ø 7.6 mm, Euro profile) and is compatible with all popular systems.

Technical description

Flow rate	2250 l/min
Material	Steel coupling
Connection external thread	1/4 in
maximum operating pressure	16 bar

Type of product

Coupling