



PU coiled hose 1/4 inch with eSafe steel safety coupling Ø 8 × 12 mm, usable hose length: 2m



Order data

Order number	080240 2
GTIN	7391390097453
Item class	08A

Description

Version:

Very light, flexible, and abrasion-resistant PU spiral hose with good spring retention. Temperature-resistant from -20 / 60 °C. PU coiled hose 1/4 inch with eSafe steel safety coupling Ø 8×12 mm 2 m ISO B.

Supplied with:

Includes quick-release **safety** coupling No. 080285 and steel coupling adaptor No. 080290.

Technical description

Hose internal Ø	8 mm
Hose external Ø	12 mm
Material	PU spiral hose
Colour	blue
usable hose length	2 m
Connection quick-release coupling	1/4 in
maximum operating pressure	10 bar
Connection plug nipple	1/4 in

maximum bursting pressure	35 bar
Type of product	Hose

Accessories

Safety shut-off External thread Connection external thread 1/4 in	080285 1/4
Coupling adaptor with external thread 5-piece set Connection external thread 1/4 in	080290 1/4