

**Garant**
**Chamfer mill 45°, Weldon shank, Ø D: 23,5mm**

**Order data**

Order number	216100 23,5
GTIN	4045197429605
Item class	210

**Description**
**Note:**

Use GARANT torque screwdriver TQ No. **211750 size 3.8** with bit No. **674252 size 15IP**.

**Technical description**

Overhang $L_1$	30 mm
Shank $\varnothing D_s$ h6	20 mm
Overall length $L_{tot}$	130 mm
maximum chamfering $\varnothing D_{max}$	35.8 mm
Pack of insert screws	219805 (15IP; 3.8 Nm)
suitable indexable insert	SD.. 090308
Number of cutting edges Z	4
$\varnothing D$	23.5 mm
Shank type	Weldon shank
Chamfering angle reverse	45 degrees
Setting angle $\kappa$	45 degrees
Through-coolant	yes
Tool exchange	PowerCard
Type of product	Indexable end mill

---

## Accessories

Torque screwdriver, fixed setting set torque 3,8 N·m	211750 3,8
Set of insert screws 10-piece	219804
Set of insert screws 10-piece	219805
PrecisionBit for Torx Plus®, 1/4 inch E 6.3 Torx Plus® profile 15IP	674252 15IP

---