



PU coiled hose 1/4 inch with eSafe steel safety coupling Ø 8 × 12 mm, usable hose length: 4m



Order data

Order number	080240 4
GTIN	7391390108173
Item class	08A

Description

Version:

Very light, flexible, and abrasion-resistant PU spiral hose with good spring retention. Temperature-resistant from -20 / 60 °C. PU coiled hose 1/4 inch with eSafe steel safety coupling Ø 8×12 mm 4 m ISO B.

Supplied with:

Includes quick-release **safety** coupling No. 080285 and steel coupling adaptor No. 080290.

Technical description

maximum operating pressure	10 bar
Colour	blue
Connection quick-release coupling	1/4 in
usable hose length	4 m
Connection plug nipple	1/4 in
Material	PU spiral hose
Hose external Ø	12 mm
Hose internal Ø	8 mm
maximum bursting pressure	35 bar

Type of product

Hose

AccessoriesSafety shut-off External thread Connection external thread
1/4 in

080285 1/4

Coupling adaptor with external thread 5-piece set
Connection external thread 1/4 in

080290 1/4