



Air blow gun, plastic with permanently attached pipe, Length exhaust pipe: 90mm



Order data

| | |
|--------------|---------------|
| Order number | 080250 90 |
| GTIN | 2050000970252 |
| Item class | 08A |

Description

Version:

Compressed air guns with steplessly adjustable air flow, low weight, flexible suspension options, and easy handling.

Function:

IP20: No protection against penetration by foreign bodies with $\varnothing < 12$ mm, however touching should be avoided, and no protection against water.

Application:

For improving the performance, economics, and safety of industrial compressed air installations.

Supplied with:

Supplied with steel coupling adapter No. **080290 size 1/4** and 8 mm steel hose connector .

Note:

The CEJN series 320 satisfies Euro standard 7.6 (nominal \varnothing 7.6 mm, Euro profile) and is compatible with all popular systems.

Flow rate: 500 l/min

Technical description

| | |
|---------------------|-----------|
| Length exhaust pipe | 90 mm |
| Flow rate | 500 l/min |
| Type of product | Pistol |

Accessories

| | |
|--|------------|
| Protective shield, transparent for compressed air gun External Ø 100 mm | 080256 100 |
| Pipe nozzle and whisper-quiet nozzle set | 080257 |
| Magnetic holder kit series | 080261 |
| Coupling adaptor with external thread 5-piece set Connection external thread 1/4 in | 080290 1/4 |