

**Garant**
**Chamfer mill 45°, Weldon shank, Type: 1**

**Order data**

Order number	216550 1
GTIN	4045197685506
Item class	210

**Description**
**Note:**

Use GARANT torque screwdriver TQ No. **211750 size 1.2** with bit No. **674252 size 8IP**.

**Technical description**

suitable indexable insert	260982 HB725-1
maximum chamfering $\varnothing D_{\max}$	16 mm
Insert screw	219795 1 (8IP; 1.2 Nm)
Overall length $L_{\text{tot}}$	70 mm
Overhang $L_1$	20 mm
Shank $\varnothing D_s$ h6	12 mm
Number of cutting edges Z	1
$\varnothing D$	1.2 mm
Shank type	Weldon shank
Chamfering angle forwards	90 degrees
Setting angle $\kappa$	45 degrees
Through-coolant	yes
Tool exchange	PowerCard
Type of product	Indexable end mill

---

**Accessories**

PrecisionBit for Torx Plus®, 1/4 inch E 6.3 Torx Plus® profile 8IP	674252 8IP
Clamping screw Type 1	219795 1
Torque screwdriver, fixed setting set torque 1,2 N·m	211750 1,2