



## Safety shut-off External thread, Connection external thread: 1/2in



### Order data

|              |               |
|--------------|---------------|
| Order number | 080285 1/2    |
| GTIN         | 7391390285645 |
| Item class   | 08A           |

### Description

#### Version:

**Steel couplings** have many advantages in pneumatic systems compared to standard brass couplings:

- **Easy to use with only one hand with low coupling force.**
- **High flow rates as a consequence of very low pressure drop.**
- **Long working life due to surface treatment and hardened components with tight manufacturing tolerances.**
- **Cost-effectiveness – the amortisation time is 2 years at the most.**

The **eSafe safety coupling** satisfies the ISO standard 4414 and EN 983 It is first depressurised and then decoupled in a second step (no whiplash). New improved single-handed operation. Rate of flow: 2250 ltr/min, maximum operating pressure 16 bar.

#### Application:

For improving the performance, economics, and safety of industrial compressed air installations.

#### Note:

**The CEJN series 320 satisfies Euro standard 7.6 (nominal Ø 7.6 mm, Euro profile) and is compatible with all popular systems.**

### Technical description

|                            |                |
|----------------------------|----------------|
| Flow rate                  | 2250 l/min     |
| Material                   | Steel coupling |
| Connection external thread | 1/2 in         |
| maximum operating pressure | 16 bar         |

Type of product

Coupling