

**HOLEX**

**Indexable face mill 45°, with bore, Ø D / number of effective cutting edges Z:  
50/4mm**



## Order data

Order number	214202 50/4
GTIN	4067263001898
Item class	220

## Description

**Version:**

Without through-coolant feed.

**Note:**

Use GARANT torque screwdriver TQ No. **211750 size 5.7** with bit No. **674252 size 20IP**.

## Technical description

Overall length $L_{tot}$	48 mm
Pack of insert screws	219848 (20IP; 5.7 Nm)
suitable indexable insert	SE.. 1204..
maximum external $\varnothing D_{max}$	63 mm
Number of cutting edges Z	4
Cutting edge $\varnothing D_c$	50 mm
Mounting bore $\varnothing$	22 mm

Shank type	with bore
Setting angle $\kappa$	45 degrees
Spacing of the cutters	unequal spacing
Machining strategy	MTC
Standard	Works standard
Type of product	Face Mill

---

## Accessories

Set of insert screws 10 pieces	219848
--------------------------------	--------