



Magnetic mitre clamp, Ferrite



Order data

| | |
|--------------|---------------|
| Order number | 085966 |
| GTIN | 2050000965388 |
| Item class | 08Q |

Description

Version:

All side faces including Vees are magnetic. The **Vee faces are suitable for round material**.
Temperature-resistant up to maximum 200 °C.

Function:

IP20: No protection against penetration by foreign bodies with $\varnothing < 12$ mm, however touching should be avoided, and no protection against water.

Application:

For powerful rigid support of round components (pipe \varnothing up to 76 mm) in a variety of angular positions.

maximum nominal clamping force: 680 N

Height: 45 mm

Length: 184 mm

Thickness: 43 mm

Weight: 1.65 kg

Technical description

| | |
|--------------------------------|-------|
| Thickness | 43 mm |
| maximum nominal clamping force | 680 N |
| maximum pipe \varnothing | 76 mm |

| | |
|--------------------------------|----------------------|
| maximum temperature resistance | 200 °C |
| Weight | 1.65 kg |
| Length | 184 mm |
| Height | 45 mm |
| pre-set angle | 45 ° |
| Material of the magnet core | Ferrite |
| Type of product | Magnetic mitre clamp |