



Telescopic multi-purpose ladder 4-part, Number of rungs: 4X6



Order data

Order number	966111 4X6
GTIN	4003866413850
Item class	96Z

Description

Version:

Multi-functional lean-to ladder, stepladder, and staircase stepladder in one. For all variants the working height is adjustable in rung spacings of 280 mm. Rung-stile connection by strong high quality flanging. Compact transport size, space-saving. Easy to use, automatically engaging aluminium plate safety catch. Safe height adjustment by means of 4 pull clips of die-cast aluminium. With swing-out stabilisers for use as a lean-to ladder to EN 131-1 (not for size 4x3). The stabilisers can be folded in to save space either during transport or when used as a stepladder.

Standard:

DIN EN 131.

Technical description

Weight	22 kg
Length closed	1.86 m
Stepladder working height approx.	4.4 m
Depth closed	0.21 m

Type of step	Rung
Lean-to ladder working height approx.	7.1 m
Width closed	0.78 m
Ladder length extended	6.4 m
Number of steps	4×6
Standard	DIN EN 131-2
Ladders and platforms load capacity	150 kg
Type of product	Multi-purpose ladder