



Telescopic multi-purpose ladder 4-part, Number of rungs: 4X5



Order data

| | |
|--------------|---------------|
| Order number | 966111 4X5 |
| GTIN | 4003866413843 |
| Item class | 96Z |

Description

Version:

Multi-functional lean-to ladder, stepladder, and staircase stepladder in one. For all variants the working height is adjustable in rung spacings of 280 mm. Rung-stile connection by strong high quality flanging. Compact transport size, space-saving. Easy to use, automatically engaging aluminium plate safety catch. Safe height adjustment by means of 4 pull clips of die-cast aluminium. With swing-out stabilisers for use as a lean-to ladder to EN 131-1 (not for size 4x3). The stabilisers can be folded in to save space either during transport or when used as a stepladder.

Standard:

DIN EN 131.

Technical description

| | |
|-----------------------------------|--------|
| Weight | 18 kg |
| Stepladder working height approx. | 3.85 m |
| Length closed | 1.58 m |
| Number of steps | 4x5 |

| | |
|---------------------------------------|----------------------|
| Depth closed | 0.21 m |
| Standard | DIN EN 131-2 |
| Width closed | 0.71 m |
| Lean-to ladder working height approx. | 6.05 m |
| Type of step | Rung |
| Ladder length extended | 5.3 m |
| Ladders and platforms load capacity | 150 kg |
| Type of product | Multi-purpose ladder |