



Telescopic multi-purpose ladder 4-part, Number of rungs: 4X3



Order data

Order number	966111 4X3
GTIN	4003866419340
Item class	96Z

Description

Version:

Multi-functional lean-to ladder, stepladder, and staircase stepladder in one. For all variants the working height is adjustable in rung spacings of 280 mm. Rung-stile connection by strong high quality flanging. Compact transport size, space-saving. Easy to use, automatically engaging aluminium plate safety catch. Safe height adjustment by means of 4 pull clips of die-cast aluminium. With swing-out stabilisers for use as a lean-to ladder to EN 131-1 (not for size 4x3). The stabilisers can be folded in to save space either during transport or when used as a stepladder.

Standard:

DIN EN 131.

Technical description

Width closed	0.5 m
Lean-to ladder working height approx.	3.85 m
Type of step	Rung
Ladder length extended	2.98 m

Stepladder working height approx.	2.75 m
Length closed	1.05 m
Depth closed	0.21 m
Number of steps	4×3
Standard	DIN EN 131-2
Weight	9 kg
Ladders and platforms load capacity	150 kg
Type of product	Multi-purpose ladder