

Garant GREENPLUS

**GARANT GreenPlus Power Force, Contents (ml or l): 200****Order data**

Order number	088006 200
GTIN	4067263120551
Item class	01L

**Description****Version:**

NSF certification. Suitable for use in the food industry.

**Extreme degreasing power** through hybrid technology. Burnt-in contamination, special greases, oils, soot, rubber residue, bitumen, waxes and pastes are loosened using plant extracts and quickly removed from the surface using surfactant technology. 200-litre plastic drum.

Power Force is a water-based, low-foaming cleaner, based on sustainable raw materials. The natural active ingredients effectively remove dirt without corroding the surfaces. A pleasant aroma and lack of solvents and VOCs make it the perfect companion for successful and safe working. Power Force represents an effective alternative to solvents. In addition to manual use, it can also be used in component cleaning devices. In this kind of use, the cleaner can be used multiple times and supports the closed cycle approach. This not only saves resources, but also avoids waste. Due to NSF certification, the cleaner can be used not only for maintenance but also in the foodstuffs industry.

- **Carries no hazard labels.**
- **Can be used manually and with a machine.**
- **NSF-certified for the foodstuffs industry.**
- **For refilling spray bottles and pressure sprayers.**

**Technical description**

Operating temperature range	2 - 40 °C
Boiling point	100 °C
Colour	transparent
Sustainability	GARANT GreenPlus
Shape	liquid
pH value	10.5 - 11
Contents	200 l
Storage temperature	2 - 35 °C
Density	1.007 g/cm <sup>3</sup>
Version	Barrel
Series	GreenPlus
Type of product	Universal cleaner