



MultiMaster MM 700 Max Top Cordless, Type: 71293661



Order data

Order number	077806 71293661
GTIN	4014586895277
Item class	03F

Description

Version:

Market-leading oscillating tools in three different performance classes (SuperCut, MultiMaster, MultiTalent) in a new version with **Starlock tool arbor** (improved torque transmission of up to 35 % greater rate of progression of the work).

- **Virtually unlimited application possibilities (sawing, grinding, scraping, cutting, rasping) due to the oscillating mode of movement (low generation of dust).**
- **Stepless electronic speed control for optimum working.**
- **Very high quality and stability thanks to the metal gearbox and use of ball bearings and needle bearings throughout.**
- **Optimum handling due to ergonomic design with soft-grip inlays and low weight.**

Most suitable MultiTool for rapid work progress (for interior work and renovating) with bi-metal saw blade for wood, metal and plastics. Thanks to the StarlockMax arbor, you have access to around 180 FEIN accessories from the Starlock, StarlockPlus and StarlockMax performance classes.

Supplied with:

60-piece accessory set, charger, 2x AMPShare Li-ion rechargeable battery (18 V / 4 Ah), dust extractor, L-BOXX. 2 pcs. curved E-Cut standard saw blades (35 mm), 2 pcs. curved E-Cut standard saw blades (65 mm), 1 pc. E-Cut precision saw blade (35 mm), 1 pc. E-Cut precision saw blade (65 mm), 1 pc. E-Cut long-life saw blade (10 mm), 2 pcs. E-Cut long-life saw blades (35 mm), 1 pc. E-Cut long-life saw blade (32 mm), 1 pc. E-Cut long-life saw blade (42 mm), 1 pc. E-Cut Carbide Pro saw blade (32 mm), 1 pc. segmented saw blade (Ø 85 mm), 1 pc. carbide segmented saw blade, 1 pc. carbide rasp (three-square), 1 pc. scraper, 1 pc. mushroom-shaped cutting blade, 1 pc. multi-purpose knife, 1 pc. perforated abrasive plate, 10 pcs. each perforated abrasive sheets (grit 60, 80,

120, 180), 1 pc. dust extractor, 1 pc. quick charger GAL 1880 CV, 2 pcs. Li-ion battery packs (18 V / 4 Ah), 1 pc. plastic tool case (L-Boxx 136).

Note:

See No. 073851 – 073858 for suitable batteries.

Technical description

Battery voltage	18 V
Amplitude (oscillation movement)	2 × 2.0 degrees
Manufacturer's designation	AMM 700 Max TOP
Power supply	Battery-powered
Type of rechargeable battery	Lithium-ion
Number of rechargeable batteries contained	2
Speed of oscillation	10000 - 19500 min ⁻¹
Toolholder	StarlockMax
Weight	1.8 kg
Battery capacity	4 Ah
Packaging	Modular case (L-Boxx)
suitable battery - supplier / battery type / voltage	Bosch 18 V
Type of product	Oscillators

Accessories

Segmented saw blade, carbide Saw blade Ø 90 mm	077828 90
Segmented saw blade, carbide, 2.2 mm Saw blade Ø 90 mm	077865 90
Saw blade, bi-metal HSS Saw blade Ø 100 mm	077838 100
Saw blade, solid HSS, 5 pieces Saw blade Ø 85 mm	077835 85
Battery starter set Type 92604323	073832 92604323
E-Cut saw blade set, wood + metal 6 pieces Version SET	077848 SET
E-Cut saw blade, diamond Width of cut 44 mm	077885 44

E-Cut saw blade, Carbide Pro Cutting width 35 mm	077891 35
E-Cut saw blade, diamond, 2.2 mm	077886
E-Cut saw blade, bi-metal, long-Life Width of cut 42 mm	077884 42
Saw blade, bi-metal HSS, 5 pieces Saw blade Ø 85 mm	077839 85
Segmented saw blade, diamond, 2.2 mm Saw blade Ø 90 mm	077867 90
Battery starter set Type 92604324	073832 92604324
E-Cut saw blade, standard, 5 pieces Width of cut 35 mm	077840 35
E-Cut saw blade, diamond, SLP mount Cutting width 35 mm	077849 35
Battery starter set Type 92604325	073832 92604325
Segmented saw blade, diamond, 1.2 mm Saw blade Ø 75 mm	077830 75
E-Cut saw blade, standard Cutting width 65 mm	077844 65
E-Cut saw blade, curved Cutting width 35 mm	077870 35
Saw blade, bi-metal HSS, 5 pieces Saw blade Ø 100 mm	077839 100
Li-ion battery Rechargeable battery type, battery voltage FE18 V	073837 FE18
E-Cut saw blade, bi-metal, Universal Width of cut 44 mm	077856 44
E-Cut saw blade, standard Cutting width 35 mm	077844 35
Segmented saw blade, solid HSS Saw blade Ø 85 mm	077836 85
E-Cut saw blade, bi-metal, Fine Width of cut 30 mm	077857 30
Carbide rasp, 3-square	077888
MultiMaster MM 700 Max TopCordless Type 71293462	077805 71293462
Segmented saw blade, diamond Saw blade Ø 90 mm	077868 90
Segmented saw blade, carbide, 1.2 mm Saw blade Ø 90 mm	077829 90
E-Cut saw blade, bi-metal, long-Life Width of cut 32 mm	077884 32
E-Cut saw blade, bi-metal, Precision Width of cut 35 mm	077850 35
E-Cut saw blade, bi-metal, Long-Life Cutting width 20 mm	077847 20
E-Cut saw blade, carbide, SLP mount Width of cut 35 mm	077858 35

Segmented saw blade, bi-metal HSS Saw blade Ø 100 mm	077827 100
Segmented saw blade, diamond, 1.2 mm Saw blade Ø 90 mm	077830 90
E-Cut saw blade, diamond, 1.2 mm	077887
Saw blade, solid HSS Saw blade Ø 85 mm	077834 85
Segmented saw blade, diamond, 2.2 mm Saw blade Ø 75 mm	077867 75
E-Cut saw blade, Carbide Pro Cutting width 35 mm	077893 35
Saw blade, bi-metal HSS Saw blade Ø 85 mm	077838 85
E-Cut saw blade, standard, 5 pieces Width of cut 65 mm	077840 65
Segmented saw blade, carbide, 2.2 mm Saw blade Ø 75 mm	077865 75
E-Cut saw blade set, MiniCut3 pieces Version SET	077859 SET
E-Cut saw blade, curved Cutting width 50 mm	077870 50
Segmented saw blade, carbide, 1.2 mm Saw blade Ø 75 mm	077829 75