



LED rechargeable rod lamp, Length: 220mm



Order data

Order number	081564 220
GTIN	4067263252566
Item class	02A

Description

Version:

Foldable and slim LED cordless work lamps with **three lighting options**. Can be used in many applications due to the slim design and two magnets.

- **One spotlight and two main lights.**
- **Front main light dimmable in 2 light levels.**
- **can be folded 180°.**
- **Battery charge is always clearly visible through the LED display.**

Function:

IP20: Protected against penetration by foreign bodies with $\varnothing < 12$ mm, however touching should be avoided, and offers no protection against water.

Supplied with:

Supplied with USB-C charging cable.

Technical description

IP Index of Protection	IP 20
Weight	61 g

Number of rechargeable batteries contained	1
Type of rechargeable battery	Lithium-ion
Bulb	LED module
Power supply	Mains operated
Illumination	50 - 100 lm
Illumination time	3 - 6 h
Overall width	30 mm
Type of product	Inspection lamp