

**Fabric adhesive tape, grey, Type: 48X50****Order data**

Order number	083602 48X50
GTIN	4063565117909
Item class	08M

Description**Version:**

tesa® 74662 duct tape bonds with excellent adhesive strength even on rough and dusty substrates. It is waterproof, supple and flexible. Ideal for sealing pipes and cables, and for applications on plasterwork and masonry. It can easily be torn by hand both across and along the tape.

Note:

The specified "best before" date for tesa® products is in relation to compliance with the specified storage guidelines.

New dimension: tesa fabric tapes 74662 are 2 mm wider (50x50)!

Technical description

Type of adhesive tape	single-sided
Application	Binding
Application	Bonding
Application	Securing
Application	Sealing

Application	Packing
Application	Attaching
Special features	tearable by hand
Special features	supple
Special features	water-repellent
Storage humidity	50 - 70 %
Width	50 mm
temperature-resistant up to	60 °C
Backing material	PE film
Stretch capability	19 %
Length	50 m
Adhesive strength on steel	0.44 N/mm
Colour	grey
Storage temperature	15 - 35 °C
Fabric fineness	27 mesh
Adhesive	Synthetic rubber
Tensile strength	3 N/mm
Thickness	0.215 mm
Liner present	no
Manufacturer's designation	duct tape 74662
Product name attribute	grey
Type of product	Adhesive tape