



Fabric adhesive tape, black, Type: 48X50



Order data

Order number	083603 48X50
GTIN	4063565117893
Item class	08M

Description

Version:

tesa® 74662 duct tape bonds with excellent adhesive strength even on rough and dusty substrates. It is waterproof, supple and flexible. Ideal for sealing pipes and cables, and for applications on plasterwork and masonry. It can easily be torn by hand both across and along the tape.

Note:

The specified "best before" date for tesa® products is in relation to compliance with the specified storage guidelines.

New dimension: tesa fabric tapes 74662 are 2 mm wider (50x50)!

Technical description

Backing material	PE film
Application	Securing
Application	Attaching
Application	Bonding
Application	Binding

Application	Packing
Application	Sealing
Length	50 m
Adhesive strength on steel	0.44 N/mm
Manufacturer's designation	duct tape 74662
Storage humidity	50 - 70 %
Special features	water-repellent
Special features	supple
Special features	can be torn by hand
Adhesive	Synthetic rubber
Thickness	0.215 mm
Tensile strength	3 N/mm
Colour	black
temperature-resistant up to	60 °C
Stretch capability	19 %
Type of adhesive tape	single-sided
Fabric fineness	27 mesh
Width	38 mm
Storage temperature	15 - 35 °C
Liner present	no
Product name attribute	black
Type of product	Adhesive tape