


SOMT.....ER-FL, CA6535, Type: 14

Order data

Order number	222092 14
GTIN	4960664708284
Item class	25A

Description
Version:

4-edge indexable inserts with convex cutting edges for low cutting forces.

Application:

FL geometry (surface-oriented) is the first choice for roughing on lower-powered machines. Do not use for helical, plunging or contour milling, or on steep walls.

Note:

Standard application values for $a_e = 0.3 \times D$.

Technical description

Feed f_z per tooth	0.2 – 1.2 mm
Type	S
Programming radius at $a_{p\max}$	3 mm
Corner radius	1.4 mm
Insert thickness E	5.56 mm
Indexable insert size	14

ISO code indexable insert	SOMT140520ER-FL
Grade	CA6535
Tool material	Carbide
Number of changes/inserts	4
Type of product	Indexable insert for milling

User data

	Suitability	V_c	ISO code
Inconel	suitable	30 m/min	S
wet maximum	suitable only under restricted conditions		
dry	suitable		
Air	suitable		