



## MultiMaster MM 700 Max Top 0 version, Type: 71293663



### Order data

|              |                 |
|--------------|-----------------|
| Order number | 077807 71293663 |
| GTIN         | 4014586895291   |
| Item class   | 03F             |

### Description

#### Version:

Market-leading oscillating tools in three different performance classes (SuperCut, MultiMaster, MultiTalent) in a new version with **Starlock tool arbor** (improved torque transmission of up to 35 % greater rate of progression of the work).

- **Virtually unlimited application possibilities (sawing, grinding, scraping, cutting, rasping) due to the oscillating mode of movement (low generation of dust).**
- **Stepless electronic speed control for optimum working.**
- **Very high quality and stability thanks to the metal gearbox and use of ball bearings and needle bearings throughout.**
- **Optimum handling due to ergonomic design with soft-grip inlays and low weight.**

Most suitable MultiTool for rapid work progress (for interior work and renovating) with bi-metal saw blade for wood, metal and plastics. Thanks to the StarlockMax arbor, you have access to around 180 FEIN accessories from the Starlock, StarlockPlus and StarlockMax performance classes.

#### Supplied with:

2 pcs. curved E-Cut standard saw blades (35 mm), 2 pcs. curved E-Cut standard saw blades (65 mm), 1 pc. E-Cut precision saw blade (35 mm), 1 pc. E-Cut precision saw blade (65 mm), 1 pc. E-Cut long-life saw blade (10 mm), 2 pcs. E-Cut long-life saw blades (35 mm), 1 pc. E-Cut long-life saw blade (32 mm), 1 pc. E-Cut long-life saw blade (42 mm), 1 pc. E-Cut Carbide Pro saw blade (32 mm), 1 pc. segmented saw blade (Ø 85 mm), 1 pc. carbide segmented saw blade, 1 pc. carbide rasp (three-square), 1 pc. scraper, 1 pc. mushroom-shaped cutting blade, 1 pc. multi-purpose knife, 1 pc. perforated abrasive plate, 10 pcs. each perforated abrasive sheets (grit 60, 80, 120, 180), 1 pc. dust extractor, 1 pc. plastic tool case (L-Boxx 136). 0 version (without battery).

## Technical description

|  |   |
|--|---|
| Power supply   | Mains operated                          |
| Manufacturer's designation                           | MULTIMASTER AMM<br>700 MAX TOP AS 18V/- |
| Battery voltage                                      | 18 V                                    |
| Number of rechargeable batteries contained           | 0                                       |
| Speed of oscillation                                 | 10 - 19500 min <sup>-1</sup>            |
| Type of rechargeable battery                         | Lithium-ion                             |
| Packaging  | Carrying case                           |
| suitable battery - supplier / battery type / voltage | Bosch 18 V                              |
| Type of product                                      | Oscillators                             |

## Accessories

|   |            |
|---|------------|
| Carbide rasp, 3-square                                  | 077888     |
| E-Cut saw blade, standard, 5 pieces Width of cut 35 mm  | 077840 35  |
| Segmented saw blade, diamond, 1.2 mm Saw blade Ø 90 mm  | 077830 90  |
| Saw blade, bi-metal HSS Saw blade Ø 85 mm               | 077838 85  |
| Saw blade, solid HSS Saw blade Ø 85 mm                  | 077834 85  |
| E-Cut saw blade, bi-metal, Fine Width of cut 30 mm      | 077857 30  |
| E-Cut saw blade, bi-metal, long-Life Width of cut 32 mm | 077884 32  |
| E-Cut saw blade, diamond, 1.2 mm                        | 077887     |
| E-Cut saw blade, curved Cutting width 50 mm             | 077870 50  |
| E-Cut saw blade set, MiniCut3 pieces Version SET        | 077859 SET |
| E-Cut saw blade, bi-metal, long-Life Width of cut 42 mm | 077884 42  |
| Segmented saw blade, carbide Saw blade Ø 90 mm          | 077828 90  |
| E-Cut saw blade, standard Cutting width 35 mm           | 077844 35  |

|  |                 |
|--|-----------------|
| E-Cut saw blade, diamond, SLP mount Cutting width 35 mm  | 077849 35       |
| Segmented saw blade, diamond, 2.2 mm Saw blade Ø 75 mm   | 077867 75       |
| E-Cut saw blade, standard, 5 pieces Width of cut 65 mm   | 077840 65       |
| Saw blade, bi-metal HSS Saw blade Ø 100 mm               | 077838 100      |
| Segmented saw blade, carbide, 2.2 mm Saw blade Ø 75 mm   | 077865 75       |
| Segmented saw blade, carbide, 2.2 mm Saw blade Ø 90 mm   | 077865 90       |
| E-Cut saw blade, Carbide Pro Cutting width 35 mm         | 077893 35       |
| E-Cut saw blade, standard Cutting width 65 mm            | 077844 65       |
| MultiMaster MM 700 Max TopCordless Type 71293462         | 077805 71293462 |
| E-Cut saw blade, carbide, SLP mount Width of cut 35 mm   | 077858 35       |
| Saw blade, bi-metal HSS, 5 pieces Saw blade Ø 85 mm      | 077839 85       |
| E-Cut saw blade, bi-metal, Universal Width of cut 44 mm  | 077856 44       |
| Segmented saw blade, diamond Saw blade Ø 90 mm           | 077868 90       |
| E-Cut saw blade, Carbide Pro Cutting width 35 mm         | 077891 35       |
| Segmented saw blade, diamond, 2.2 mm Saw blade Ø 90 mm   | 077867 90       |
| Segmented saw blade, bi-metal HSS Saw blade Ø 100 mm     | 077827 100      |
| E-Cut saw blade, curved Cutting width 35 mm              | 077870 35       |
| Saw blade, bi-metal HSS, 5 pieces Saw blade Ø 100 mm     | 077839 100      |
| E-Cut saw blade, diamond, 2.2 mm                         | 077886          |
| E-Cut saw blade, bi-metal, Long-Life Cutting width 20 mm | 077847 20       |
| E-Cut saw blade, diamond Width of cut 44 mm              | 077885 44       |
| Segmented saw blade, carbide, 1.2 mm Saw blade Ø 75 mm   | 077829 75       |
| Segmented saw blade, carbide, 1.2 mm Saw blade Ø 90 mm   | 077829 90       |
| E-Cut saw blade, bi-metal, Precision Width of cut 35 mm  | 077850 35       |
| E-Cut saw blade set, wood + metal 6 pieces Version SET   | 077848 SET      |

|  |            |
|--|------------|
| Segmented saw blade, solid HSS Saw blade Ø 85 mm               | 077836 85  |
| Saw blade, solid HSS, 5 pieces Saw blade Ø 85 mm               | 077835 85  |
| Segmented saw blade, diamond, 1.2 mm Saw blade Ø 75 mm         | 077830 75  |
| Li-ion batteryProCore Battery type, battery voltage C18 V      | 073856 C18 |
| Battery starter setProCore Battery type, battery voltage C18 V | 073867 C18 |