



Base body Parallel shank, with through-coolant, 5×D, Type: 18



Order data

| | |
|--------------|---------------|
| Order number | 232250 18 |
| GTIN | 4045197589057 |
| Item class | 22G |

Description

Version:

With internal cooling.

Note:

Further sizes available on request.

Through-coolant: yes

Number of cutting edges Z: 2

Dia. range D_c : 18 - 24 mm

Reach L_1 : 168.3 mm

Shank $\varnothing D_s$: 25 mm

Shank length L_s : 56 mm

Clamping screws: 232990 TX9

Technical description

| | |
|---------------------------|------------|
| Clamping screws | 232990 TX9 |
| Shank $\varnothing D_s$ | 25 mm |
| Dia. range D_c | 18 - 24 mm |
| Reach L_1 | 168.3 mm |
| Shank length L_s | 56 mm |
| Number of cutting edges Z | 2 |
| Version | 5×D |
| Shank | ISO 9766 |
| Through-coolant | yes |

Type of product

Indexable drill

Accessories

| | |
|---|------------|
| Torx® set of screws 10 pieces Drive TX9 | 232990 TX9 |
| PrecisionBit for Torx®, shank E 6.3 Torx® profile TX9 | 674248 TX9 |
| Torx® set of screws 10 pieces Drive TX8 | 232990 TX8 |
| Torque screwdriver, fixed setting set torque 2,2 N·m | 211750 2,2 |