



Base body MT shank, without through-coolant, 8xD, Type: 12



Order data

Order number	232265 12
GTIN	4045197592613
Item class	22G

Description

Note:

Further sizes available on request.

For suitable reducing adapters for tools with MT shanks see **No. 343000-343530**.

Reduce feed rates f by 5% and v_c values by 10%.

Through-coolant: no

Number of cutting edges Z : 2

Dia. range D_c : 12 - 12.5 mm

Reach L_1 : 111.1 mm

Morse taper MT size: 2

Clamping screws: 232990 TX7

Technical description

Reach L_1	111.1 mm
Dia. range D_c	12 - 12.5 mm
Clamping screws	232990 TX7
Morse taper MT size	2
Number of cutting edges Z	2
Version	8xD
Shank	Morse taper
Through-coolant	no
Type of product	Indexable drill

Accessories

PrecisionBit for Torx®, shank E 6.3 Torx® profile TX7	674248 TX7
Torx® set of screws 10 pieces Drive TX7	232990 TX7
Torque screwdriver, fixed setting set torque 0,6 N·m	211750 0,6