

Garant
Boring bar HSS, right-hand, Shank \varnothing / insert size: 8/06mm

Order data

Order number	260022 8/06
GTIN	4067263570561
Item class	21T

Technical description

Shank $\varnothing D_s$	8 mm
Centre offset L_3	5 mm
Minimum pre-drill $\varnothing D_{min}$	10 mm
Pack of insert screws	269028 7
Setting angle κ	95 degrees
Overall length L	125 mm
Overhang L_1	40 mm
Clamping height L_2	7 mm
Insert size	6 mm
suitable indexable insert	CC.. 0602..
ISO code toolholder	AH08K SCLCR/L06
Standard	DIN 8024
Application type	right-hand
Boring depth up to	5xD
Tool material	HSS
Through-coolant	yes
Application	Internal longitudinal turning

Type of product

Boring bar

Accessories

PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8

674248 TX8

Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm

659957 500