

Garant
Boring bar HSS, left-hand, Shank \varnothing / insert size: 8/06mm

Order data

Order number	260023 8/06
GTIN	4067263103288
Item class	21T

Technical description

ISO code toolholder	AH08K SCLCR/L06
Overall length L	125 mm
Clamping height L ₂	7 mm
Shank \varnothing D _s	8 mm
Pack of insert screws	269028 7
Insert size	6 mm
Setting angle κ	95 degrees
Centre offset L ₃	5 mm
Minimum pre-drill \varnothing D _{min}	10 mm
suitable indexable insert	CC.. 0602..
Overhang L ₁	40 mm
Standard	DIN 8024
Application type	left-hand
Boring depth up to	5×D
Tool material	HSS
Through-coolant	yes
Application	Internal longitudinal turning

Type of product

Boring bar

Accessories

PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8

674248 TX8

Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm

659957 500