

**Garant****Screw-on toolholder, right-hand, Shank / insert size: 8/07mm****Order data**

Order number	260308 8/07
GTIN	4067263103905
Item class	21T

**Technical description**

Shank size	8 mm
Overall length L	60 mm
Insert size	7 mm
suitable indexable insert	DC.. 0702..
Pack of insert screws	269028 22
Functional width L <sub>4</sub>	10 mm
Head length L <sub>1</sub>	13 mm
ISO code toolholder	SDJCR/L 0808D07
Standard	DIN ISO 5610
Application type	right-hand
Through-coolant	no
Setting angle κ	93 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

---

## Accessories

Set of insert screws Type 22	269028 22
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500