

**Garant****Screw-on toolholder, neutral, Shank / insert size: 8/07mm****Order data**

Order number	260300 8/07
GTIN	4067263103295
Item class	21T

**Technical description**

suitable indexable insert	DC.. 0702..
Insert size	7 mm
Overhang L <sub>1</sub> neutral holders	7.5 mm
Shank size	8 mm
Overall length L neutral holders	60 mm
ISO code toolholder	SDNCN 0808D07
Pack of insert screws	269028 22
Functional width L <sub>4</sub> neutral holders	4 mm
Standard	DIN ISO 5610
Application type	neutral
Through-coolant	no
Setting angle $\kappa$	62.5 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

---

## Accessories

PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15

674248 TX15

Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm

659957 500