

Garant**Screw-on toolholder, left-hand, Shank / insert size: 8/07mm****Order data**

Order number	260309 8/07
GTIN	4067263570608
Item class	21T

Technical description

ISO code toolholder	SDJCR/L 0808D07
Pack of insert screws	269028 22
Overall length L	60 mm
Insert size	7 mm
Head length L ₁	13 mm
suitable indexable insert	DC.. 0702..
Shank size	8 mm
Functional width L ₄	10 mm
Standard	DIN ISO 5610
Application type	left-hand
Through-coolant	no
Setting angle κ	93 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15
Set of insert screws Type 22	269028 22
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500