

Garant
Boring bar, steel, right-hand, Shank \varnothing / insert size: 8/04mm

Order data

Order number	260344 8/04
GTIN	4067263103943
Item class	21T

Technical description

Shank $\varnothing D_s$	8 mm
Clamping height L_2	7.5 mm
suitable indexable insert	DC.. 04T0..
ISO code toolholder	A08F SDXCR/L04
Pack of insert screws	269028 26
Setting angle κ	93 degrees
Insert size	4 mm
Head length L_1	15 mm
Minimum pre-drill $\varnothing D_{min}$	9.2 mm
Centre offset L_3	5 mm
Overall length L	80 mm
Usable depth T	3 mm
Standard	DIN 8024
Application type	right-hand
Boring depth up to	3xD
Through-coolant	yes
Application	Internal longitudinal turning

Type of product

Boring bar

Accessories

PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX5

674248 TX5

Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm

659957 500