

Garant**Boring bar, steel, left-hand, Shank Ø / insert size: 8/04mm****Order data**

| | |
|--------------|---------------|
| Order number | 260345 8/04 |
| GTIN | 4067263103950 |
| Item class | 21T |

Technical description

| | |
|--------------------------------------|-------------------------------|
| Shank Ø D _s | 8 mm |
| ISO code toolholder | A08F SDXCR/L04 |
| Clamping height L ₂ | 7.5 mm |
| Centre offset L ₃ | 5 mm |
| Head length L ₁ | 15 mm |
| Minimum pre-drill Ø D _{min} | 9.2 mm |
| suitable indexable insert | DC.. 04T0.. |
| Overall length L | 80 mm |
| Usable depth T | 3 mm |
| Insert size | 4 mm |
| Setting angle κ | 93 degrees |
| Pack of insert screws | 269028 26 |
| Standard | DIN 8024 |
| Application type | left-hand |
| Boring depth up to | 3×D |
| Through-coolant | yes |
| Application | Internal longitudinal turning |

Type of product

Boring bar

Accessories

PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX5

674248 TX5

Torque screwdriver with scale, to take interchangeable
blades maximum torque 500 cNm

659957 500