

Garant
Boring bar carbide, right-hand, Shank \varnothing / insert size: 8/07mm

Order data

Order number	260320 8/07
GTIN	4067263103820
Item class	21T

Technical description

Shank $\varnothing D_s$	8 mm
Insert size	7 mm
Overall length L	125 mm
Clamping height L_2	7.6 mm
Overhang L_1	26 mm
Centre offset L_3	7 mm
Pack of insert screws	269028 7
suitable indexable insert	DC.. 0702..
Setting angle κ	107.5 degrees
Minimum pre-drill $\varnothing D_{min}$	12 mm
ISO code toolholder	E08K SDQCR/L07
Standard	DIN 8024
Application type	right-hand
Boring depth up to	8xD
Tool material	Carbide
Through-coolant	yes
Application	Internal longitudinal turning

Type of product

Boring bar

Accessories

PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8

674248 TX8

Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm

659957 500