

Garant
GARANT Master Mute boring bar, right-hand, Shank \varnothing / insert size: 20/11mm

Order data

Order number	260326 20/11
GTIN	4067263619802
Item class	29E

Description
Version:

Round shank without clamping face.

Note:

Do not clamp on the area marked S!

Technical description

ISO code toolholder	A20X SDUCR/L11
Series	Master Mute
Insert size	11 mm
Centre offset L_3	13 mm
Minimum pre-drill $\varnothing D_{\min}$	25 mm
Overall length L	177 mm
Pack of insert screws	269028 50
suitable indexable insert	DC.. 11T3..
Setting angle κ	93 degrees
Overhang L_1	100 mm
Shank $\varnothing D_s$	20 mm
non-clamping range S	120 mm
Standard	DIN 8024
Application type	right-hand

Vibration	damped
Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring bar