

Garant
GARANT Master Mute boring bar, right-hand, Shank \varnothing / insert size: 12/07mm

Order data

Order number	260326 12/07
GTIN	4067263619789
Item class	29E

Description
Version:

Round shank without clamping face.

Note:

Do not clamp on the area marked S!

Technical description

Setting angle κ	93 degrees
Pack of insert screws	269028 38
Overall length L	120 mm
Minimum pre-drill $\varnothing D_{\min}$	16 mm
suitable indexable insert	DC.. 0702..
Centre offset L_3	9 mm
Shank $\varnothing D_s$	12 mm
Series	Master Mute
Overhang L_1	60 mm
ISO code toolholder	A12X SDUCR/L07
Insert size	7 mm
non-clamping range S	72 mm
Standard	DIN 8024
Application type	right-hand

Vibration	damped
Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring bar