

**Garant**
**GARANT Master Mute boring bar, right-hand, Shank  $\varnothing$  / insert size: 16/06mm**

**Order data**

Order number	260044 16/06
GTIN	4067263622956
Item class	29E

**Description**
**Version:**

Round shank without clamping face.

**Note:**

Do not clamp on the area marked S!

**Technical description**

suitable indexable insert	CC.. 0602..
Centre offset $L_3$	11 mm
Insert size	6 mm
Shank $\varnothing D_s$	16 mm
Minimum pre-drill $\varnothing D_{min}$	20 mm
ISO code toolholder	A16X SCLCR/L06
Series	Master Mute
Pack of insert screws	269028 38
Overhang $L_1$	80 mm
Overall length L	151 mm
Setting angle $\kappa$	95 degrees
non-clamping range S	96 mm
Standard	DIN 8024
Application type	right-hand

Vibration	damped
Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring bar