

Garant
GARANT Master Mute boring bar, right-hand, Shank \varnothing / insert size: 40/11 mm

Order data

Order number	260326 40/11
GTIN	4067263622932
Item class	29E

Description
Version:

Round shank without clamping face.

Note:

Do not clamp on the area marked S!

Technical description

Pack of insert screws	269028 50
Overall length L	343 mm
Minimum pre-drill $\varnothing D_{\min}$	50 mm
Insert size	11 mm
ISO code toolholder	A40X SDUCR/L11
Series	Master Mute
Centre offset L_3	27 mm
suitable indexable insert	DC.. 11T3..
Shank $\varnothing D_s$	40 mm
Overhang L_1	200 mm
Setting angle κ	93 degrees
non-clamping range S	240 mm
Standard	DIN 8024
Application type	right-hand

Vibration	damped
Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring bar