

Garant
GARANT Master Mute boring bar, right-hand, Shank \varnothing / insert size: 32/09mm

Order data

Order number	260044 32/09
GTIN	4067263622987
Item class	29E

Description
Version:

Round shank without clamping face.

Note:

Do not clamp on the area marked S!

Technical description

suitable indexable insert	CC.. 09T3..
Centre offset L_3	22 mm
Shank $\varnothing D_s$	32 mm
Overhang L_1	160 mm
Pack of insert screws	269028 50
Setting angle κ	95 degrees
Minimum pre-drill $\varnothing D_{min}$	40 mm
ISO code toolholder	A30X SCLCR/L09
Overall length L	277 mm
Insert size	9 mm
Series	Master Mute
non-clamping range S	192 mm
Standard	DIN 8024
Application type	right-hand

Vibration	damped
Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring bar