

Garant
GARANT Master Mute boring bar, right-hand, Shank \varnothing / insert size: 12/06mm

Order data

Order number	260044 12/06
GTIN	4067263622949
Item class	29E

Description
Version:

Round shank without clamping face.

Note:

Do not clamp on the area marked S!

Technical description

Insert size	6 mm
Pack of insert screws	269028 38
suitable indexable insert	CC.. 0602..
Centre offset L_3	8.5 mm
Series	Master Mute
Shank $\varnothing D_s$	12 mm
Minimum pre-drill $\varnothing D_{min}$	16 mm
Overall length L	120 mm
ISO code toolholder	A12X SCLCR/L06
Setting angle κ	95 degrees
Overhang L_1	60 mm
non-clamping range S	72 mm
Standard	DIN 8024
Application type	right-hand

Vibration	damped
Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring bar