

**Garant**
**GARANT Master Mute boring bar, right-hand, Shank  $\varnothing$  / insert size: 20/09mm**

**Order data**

Order number	260044 20/09
GTIN	4067263622963
Item class	29E

**Description**
**Version:**

Round shank without clamping face.

**Note:**

Do not clamp on the area marked S!

**Technical description**

Series	Master Mute
Minimum pre-drill $\varnothing D_{\min}$	25 mm
ISO code toolholder	A20X SCLCR/L09
Setting angle $\kappa$	95 degrees
Insert size	9 mm
Overall length L	177 mm
Pack of insert screws	269028 50
suitable indexable insert	CC.. 09T3..
Overhang $L_1$	100 mm
Shank $\varnothing D_s$	20 mm
Centre offset $L_3$	13 mm
non-clamping range S	120 mm
Standard	DIN 8024
Application type	right-hand

Vibration	damped
Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring bar