

Garant
GARANT Master Mute boring bar, left-hand, Shank \varnothing / insert size: 32/11 mm

Order data

Order number	260327 32/11
GTIN	4067263623359
Item class	29E

Description
Version:

Round shank without clamping face.

Note:

Do not clamp on the area marked S!

Technical description

Overall length L	277 mm
Insert size	11 mm
Pack of insert screws	269028 50
Shank $\varnothing D_s$	32 mm
suitable indexable insert	DC.. 11T3..
Centre offset L_3	22 mm
Minimum pre-drill $\varnothing D_{min}$	40 mm
Series	Master Mute
Setting angle κ	93 degrees
Overhang L_1	160 mm
ISO code toolholder	A32X SDUCR/L11
non-clamping range S	192 mm
Standard	DIN 8024
Application type	left-hand

Vibration	damped
Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring bar