

Garant
GARANT Master Mute boring bar, left-hand, Shank \varnothing / insert size: 40/11 mm

Order data

Order number	260327 40/11
GTIN	4067263623366
Item class	29E

Description
Version:

Round shank without clamping face.

Note:

Do not clamp on the area marked S!

Technical description

suitable indexable insert	DC.. 11T3..
Pack of insert screws	269028 50
ISO code toolholder	A40X SDUCR/L11
Overall length L	343 mm
Overhang L ₁	200 mm
Centre offset L ₃	27 mm
Insert size	11 mm
Series	Master Mute
Shank \varnothing D _s	40 mm
Minimum pre-drill \varnothing D _{min}	50 mm
Setting angle κ	93 degrees
non-clamping range S	240 mm
Standard	DIN 8024
Application type	left-hand

Vibration	damped
Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring bar