

**Garant**
**GARANT Master Mute boring bar, left-hand, Shank  $\varnothing$  / insert size: 25/11 mm**

**Order data**

Order number	260327 25/11
GTIN	4067263623342
Item class	29E

**Description**
**Version:**

Round shank without clamping face.

**Note:**

Do not clamp on the area marked S!

**Technical description**

Overhang $L_1$	125 mm
Overall length $L$	222 mm
Centre offset $L_3$	17 mm
Series	Master Mute
ISO code toolholder	A25X SDUCR/L11
Insert size	11 mm
Minimum pre-drill $\varnothing D_{\min}$	32 mm
Pack of insert screws	269028 50
Setting angle $\kappa$	93 degrees
suitable indexable insert	DC.. 11T3..
Shank $\varnothing D_s$	25 mm
non-clamping range S	155 mm
Standard	DIN 8024
Application type	left-hand

Vibration	damped
Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring bar