

**Garant**
**GARANT Master Mute boring bar, left-hand, Shank  $\varnothing$  / insert size: 12/07mm**

**Order data**

Order number	260327 12/07
GTIN	4067263623311
Item class	29E

**Description**
**Version:**

Round shank without clamping face.

**Note:**

Do not clamp on the area marked S!

**Technical description**

Setting angle $\kappa$	93 degrees
Series	Master Mute
Insert size	7 mm
Shank $\varnothing D_s$	12 mm
Overall length L	120 mm
suitable indexable insert	DC.. 0702..
Centre offset $L_3$	9 mm
Pack of insert screws	269028 38
ISO code toolholder	A12X SDUCR/L07
Overhang $L_1$	60 mm
Minimum pre-drill $\varnothing D_{min}$	16 mm
non-clamping range S	72 mm
Standard	DIN 8024
Application type	left-hand

Vibration	damped
Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring bar